

Cost-effective filter bags for demanding applications

Eaton's ABP filter bags are suitable for a wide range of applications such as beverage filtration, fine particle removal in parts cleaning, activated carbon removal in process systems, the final filtration of vinegar, lacquers, hydraulic oils and lubricants and many more.

With efficiencies greater than 99%, each ABP filter bag model provides cost-effective filtration solutions for demanding applications. The four models ensure that users can efficiently remove particles ranging from 1 – 25 µm while delivering a long service life.

Features and benefits

- ABP polypropylene filter bags are fabricated from hydrophobic microfiber filter material, which require pre-wetting with an aqueous solution (full details about wetting and installation are provided with every box of ABP filter bags)
- Highly efficient melt-blown filter material in polypropylene with graded density profiles to maximize dirt-holding capacity and prolong service life
- No additives such as resins, binders or surface treatments
- Spunbond polypropylene cover layer virtually eliminates fiber migration

- Unique UNI-WELD process for bottom seam provides a stronger, more flexible weld
- Fully-welded construction with patented SENTINEL® seal ring provides 100% bypass-free filtration
- The pressure-activated SENTINEL seal ring provides a flexible, chemically resistant seal which adapts to any bag filter housing

Filter specifications

Material

Melt-blown polypropylene

Cover layer

Spunbond polypropylene

Seal ring

Welded polypropylene SENTINEL seal ring

Retention ratings¹

1, 5, 10, 25 μm @ > 99% efficiency

Dimensions/Parameters

عمحن

03: Ø 100 x 230 mm L 04: Ø 100 x 380 mm L

Filter area

03: 0.08 m² 04: 0.16 m²

Max. operating temperature

Polypropylene: 90 °C

Max. differential pressure

2.5 bar

Recommended change-out pressure for disposal²

0.8 – 1.5 bar

Max. flow rates³


03: 3 m³/h 04: 5 m³/h

FDA/EC conformity

All polypropylene materials used in manufacturing comply with the regulations of the Food and Drug Administration (FDA), title 21 of the Code of Federal Regulations Section 177, and EC Regulations 1935/2004 and EC Directive 2002/72/EC, as applicable for food and beverage contact.




Flow rates



Filter removal efficiency

| Retention ratings ¹ (µm) | Particle size (μm) at common removal efficiencies (%) | | | | Max. operating temperature |
|---|--|-------|-------|-------|-------------------------------|
| | > 60% | > 90% | > 95% | > 99% | (°C) |
| 1 | - | 1 | 2 | 4 | 90 |
| 5 | 1 | 2 | 4 | 5 | 90 |
| 10 | 2 | 5 | 10 | 30 | 90 |
| 25 | 10 | 30 | 40 | - | 90 |

Ordering Information



North America

44 Apple Street Tinton Falls, NJ 07724 Toll Free: 800 656-3344 (North America only) Tel: +1 732 212-4700

Europe/Africa/Middle Fast

Auf der Heide 2 53947 Nettersheim, Germany Tel: +49 2486 809-0

Friedensstraße 41 68804 Altlußheim, Germany Tel: +49 6205 2094-0

An den Nahewiesen 24 55450 Langenlonsheim, Germany Tel: +49 6704 204-0

No. 3, Lane 280, Linhong Road Changning District, 200335 Shanghai, PR. China Tel: +86 21 5200-0099

4 Loyang Lane #04-01/02 Singapore 508914 Tel: +65 6825-1668

Brazil Av. Julia Gaioli, 474 – Bonsucesso 07251-500 – Guarulhos, Brazil Tel: +55 11 2465-8822

For more information, please email us at filtration@eaton.com or visit www.eaton.com/filtration

© 2016 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.

FN EF-FTB-17 06-2016





¹ Reference values based on single pass tests in ambient lab conditions with ISO test dust in water at 10 m³/h/size 02.

² Dependent on the respective applications and their requirements.

 $^{^{3}}$ For liquids with a dynamic viscosity of 1 mPa s @ 20 °C.